

Product Name :
Automatic Grinding Machine

Product Code :
ENGLABINGCAG460009



Description :

Automatic Grinding Machine

Technical Specification :

The automatic grinding machine provides fast grinding of cylinder specimen ends to obtain plane and parallel surfaces according to EN and ASTM standards.
Three units of $\varnothing 38$ to 100 mm or two units of $\varnothing 150$ -160 mm concrete cylinders ends can be ground simultaneously with the suitable cradle and water restraint panel.
The length of the any specimen must be longer than 70 mm.
According to ASTM and EN standards, the planeness accuracy of grinded surface is 0.05 mm. and the deviation of perpendicularity of the side with reference to the end faces is 0.5o.
The cradle which specimens are fixed on has automatic bidirectional radial displacement ability.
The safe and ergonomic design prevents the user to exposure to water and dust and provides easy access to the water inlet and outlet.
Specimen cradles and water restraint panels can easily be installed without the need for any assembly.
The equipment has selectable advance grinding time functionality by user from 50 to 400 seconds.
Optimum grinding time per end of all type specimens is 90 to 120 seconds.
Mobility of the machine is achieved with the help of the integral wheels, and all components of the system can be safely accessed for easy maintenance.
The frame is manufactured from aluminum to obtain a lighter weight and the stainless steel exterior shell assures resistance to corrosion.
The water restraint panels should be ordered separately for cubic specimens or different sized cylindrical specimens.

The preparation of concrete cylinder test specimen for compressive strength test
EN 12390-1, 12390-3, ASTM C31, C39, C192, C617

The maximum tolerance on the flatness of the potential load bearing surfaces (the ends of compression test specimens) is 0.002 in. [0.050 mm]

The preparation of drilled concrete cores specimen for compressive strength test
EN 12504-1, 12390-1, 12390-3 ASTM C42, C397

The deviation of perpendicularity of the side, with reference to o the end faces is 5



Engineering Lab Equipment India